

Flat suction cup (round)

SAF 80 NBR-45 G3/8-AG



Art.-Nr.: 10.01.01.11462




Technical data

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45.0 Shore A
Size	80.00
Connection	G3/8-AG
Nipple material	Aluminum

SAF 80 NBR-45 G3/8-AG

Suction cup SAF, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



Design data

Nominal diameter dn	6.00 mm
Thread G1	G3/8"-M
Key width SW1	22.0 mm
Spring stroke Z	7.6 mm
Diameter Ds	83.0 mm
Diameter Dmax(S)	89.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SAF 80 NBR-45 G3/8-AG



WWW.SCHMALZ.COM/10.01.01.11462

1

Art.-Nr.: 10.01.01.11462

**Technical data**

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	100.0 mm
Suction force (-600mbar)	272.00 N
Lateral force	205.0 N
Lateral force oily surface	180.0 N
Volume	36.700 cm ³
Size	80.00
Number of folds	0.0
Product family	SAF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Accessories 10.01.01.11462**

Typ		Item number
Suction cup cover	SU 80	10.01.01.12839

