

Bell suction cup (oval)

SAOG 80x30 NBR-45 RA



Art.-Nr.: 10.01.01.11668




Technical data

Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45.0 Shore A
Dimension (LxW)	80 x 30
Connection	RA
Nipple material	Aluminum

SAOG 80x30 NBR-45 RA

Suction cup SAOG, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



Design data

Height H	27.50 mm
Nominal diameter dn	4.00 mm
Spring stroke Z	10.0 mm
Length L4	31.80 mm
Suction cup width Bs	30.00 mm
Ls	80.00 mm
Lmax.(S)	86.00 mm
Bmax(S)	36.00 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SAOG 80x30 NBR-45 RA



WWW.SCHMALZ.COM/10.01.01.11668

1

Art.-Nr.: 10.01.01.11668

**Technical data**

Suction cup material	Nitrile rubber NBR
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Suction force (-600mbar)	105.00 N
Weight	37.10 g
Dimension (LxW)	80 x 30
Lateral force	65.0 N
Lateral force oily surface	45.0 N
Volume	13.200 cm ³
Number of folds	0.0
Product family	SAOG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

