


Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	45.0 Shore A
Dimension (LxW)	80 x 30
Connection	M10-AG
Nipple material	Steel

SAOG 80x30 NBR-45 M10-AG

Suction cup SAOG, available in various diameters, is delivered with connection nipple vulcanized to elastomer part.



Design data

Attribute	Value
Height H	24.50 mm
Nominal diameter dn	4.00 mm
Thread G1	M10-M
Thread length LG1	10.0 mm
Key width SW1	16.0 mm
Spring stroke Z	10.0 mm
Suction cup width Bs	30.00 mm
Ls	80.00 mm
Lmax.(S)	86.00 mm
Bmax(S)	36.00 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SAOG 80x30 NBR-45 M10-AG

Art.-Nr.: 10.01.01.11653

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Suction force (-600mbar)	105.00 N
Weight	30.40 g
Dimension (LxW)	80 x 30
Lateral force	65.0 N
Lateral force oily surface	45.0 N
Volume	13.200 cm ³
Number of folds	0.0
Product family	SAOG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.11653

