



Technical data


Suction cup material	Silicone SI
Material hardness [Shore A]	50.0 Shore A
Size	15.00
Material characteristics	FDA
Vacuum connection	G1/8"-M
Nipple material	Aluminum

SGPN 15 SI-50 G1/8-AG

Flat suction cup SGPN (elastomer part + connection nipple) is delivered unassembled. The delivery consists of:

- Suction cup of type SGP – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup SGP, connection nipple SA-NIP



Design data

Height H	16.00 mm
Nominal diameter dn	3.50 mm
Thread G1	G1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	0.9 mm
Diameter Ds	14.5 mm
Diameter Dmax(S)	15.5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SGPN 15 SI-50 G1/8-AG

Flat suction cup (round)

SGPN 15 SI-50 G1/8-AG



Art.-Nr.: 10.01.01.11981



Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	50.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Suction force (-600mbar)	5.50 N
Weight	4.70 g
Volume	0.278 cm ³
Size	15.00
Number of folds	0.0
Product family	SGPN

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Ordering Data Spare Parts 10.01.01.11981

Typ	Item number
Suction Cup Connection Nipples	SA-NIP N016 G1/8-AG DN350 10.01.06.05735



Ordering Data Wear Parts 10.01.01.11981

Typ	Item number
Flat suction cup (round)	SGP 15 SI-50 N016 10.01.01.10574



WWW.SCHMALZ.COM/10.01.01.11981