


Art.-Nr.: 10.01.01.12160



SAG 45 NBR-60 G1/4-IG

Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	60,0 Shore A
размер	45,00
Соединение	G1/4-IG
Материал ниппеля	алюминий



Конструктивные данные

Attribute	Value
Высота H	24,50 mm
Номинальный диаметр dn	4,00 mm
Резьба G1	G1/4"-F
Длина резьбы LG1	12,0 mm
Размер гаечного ключа SW1	17,0 mm
Ход пружины Z	7,8 mm
Диаметр Ds	47,0 mm
Диаметр Dmax(S)	51,5 mm

Конструктивные данные SAG 45 NBR-60 G1/4-IG



Art.-Nr.: 10.01.01.12160



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	60,0 Shore A
Внутренний диаметр шланга (реком.) d	4,0 mm
Радиус заготовки мин. (выпуклый)	40,0 mm
Всасывающая сила (-600 мбар)	68,00 N
Вес	14,2 g
Поперечная сила	61,0 N
Поперечная сила маслянистой поверхности	51,0 N
Объем	8,000 cm ³
размер	45,00
Количество складок	0,0
Семейство продуктов	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12160

