

Bell suction cup (round)

SAG 60 NBR-60 RA


Art.-Nr.: 10.01.01.12169



SAG 60 NBR-60 RA

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Size	60.00
Connection	RA
Nipple material	Aluminum



Design data SAG 60 NBR-60 RA

Design data

Attribute	Value
Height H	30.70 mm
Nominal diameter dn	6.00 mm
Spring stroke Z	10.6 mm
Diameter Ds	63.5 mm
Length L4	31.80 mm
Diameter Dmax(S)	70.5 mm



WWW.SCHMALZ.COM/10.01.01.12169

Art.-Nr.: 10.01.01.12169

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	50.0 mm
Suction force (-600mbar)	122.00 N
Weight	40.1 g
Lateral force	153.0 N
Lateral force oily surface	80.0 N
Volume	22.000 cm ³
Size	60.00
Number of folds	0.0
Product family	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12169

**Ordering Data Spare Parts 10.01.01.12169**

Typ		Item number
Mounting adapter	ADP-A G3/8-AG-RA ADAP	10.01.10.00234
O-ring	O-RING 19x3.2 NBR-70	10.07.08.00123

