

Bell suction cup (oval)

SAOG-S 95x40 NBR-60 RA


Art.-Nr.: 10.01.01.12182



SAOG-S 95x40 NBR-60 RA

Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Connection	RA
Dimension (LxW)	95x40
Nipple material	Aluminum



Design data SAOG-S 95x40 NBR-60 RA

Design data

Attribute	Value
Height H	24.50 mm
Nominal diameter dn	4.00 mm
Spring stroke Z	6.0 mm
Length L4	31.80 mm
Suction cup width Bs	40.60 mm
Ls	95.60 mm
Lmax.(S)	101.00 mm
Bmax(S)	46.00 mm



WWW.SCHMALZ.COM/10.01.01.12182

Art.-Nr.: 10.01.01.12182

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	35.0 mm
Suction force (-600mbar)	165.00 N
Weight	51.4 g
Dimension (LxW)	95 x 40
Lateral force	192.0 N
Lateral force oily surface	110.0 N
Volume	18.000 cm ³
Number of folds	0.0
Product family	SAOG-S

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12182

**Ordering Data Spare Parts 10.01.01.12182**

Typ		Item number
Mounting adapter	ADP-A G1/8-AG-RA ADAP	10.01.10.00210
O-ring	O-RING 10x1.5 NBR-70 GLB	10.07.08.00129
O-ring	O-RING 19x3.2 NBR-70	10.07.08.00123

**Ordering Data Wear Parts 10.01.01.12182**

Typ		Item number
Bell suction cup (oval)	SAOG-S 95x40 NBR-60 G1/8-IG	10.01.01.12180

