



Technical data


Attribute	Value
Suction cup material	Natural rubber NK
Material hardness [Shore A]	45.0 Shore A
Size	70.00
Connection	G1/4-AG
Type	E

SHFN 70 NK-45 G1/4-AG E MOS

Suction cup SHFN (elastomer part + connection nipple) is delivered assembled.
The assembly consists of:

- Suction cup of type SHF – elastomer part, available in various diameters
- Connection nipple of type SA-NIP – available with various threads
- Optional product addition: sealing ring and touch valve

Available spare parts: suction cup SHF, connection nipple SA-NIP and RED-NIP, sealing ring, touch valve
Available accessories: filter screen (sieve, round)



Design data

Attribute	Value
Height H	26.20 mm
Nominal diameter dn	4.40 mm
d2	36.0 mm
Thread G1	G1/4"-M
Thread length LG1	12.4 mm
Key width SW1	17.0 mm
Spring stroke Z	4.0 mm
Diameter Ds	70.0 mm
Diameter Dmax(S)	74.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SHFN 70 NK-45 G1/4-AG E MOS



Art.-Nr.: 10.01.01.12217

**Technical data**

Attribute	Value
Suction cup material	Natural rubber NK
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	95.0 mm
Suction force (-600mbar)	200.00 N
Weight	62.0 g
Lateral force	145.0 N
Volume	16.000 cm ³
Size	70.00
Suction force d2	100.00 N
Number of folds	0.0
Product family	SHFN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12217

**Ordering Data Accessories 10.01.01.12217**

Typ	Item number
Sieve, round	SIEB 14.5x1 MS-A2 0.103/0.15 10.05.03.00023

**Ordering Data Spare Parts 10.01.01.12217**

Typ	Item number
Reduction nipple with hexagon	RED-NIP G1/4-AG M10x1.25-AG AL 10.01.01.12194
Sealing ring	DR 46/36x5 S05 EPDM-15 KE 10.01.06.01678

