


Art.-Nr.: 10.01.01.12267



SAG 60 NBR-60 G1/4-IG

Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	60,0 Shore A
размер	60,00
Соединение	G1/4-IG
Материал ниппеля	алюминий



Конструктивные данные

Attribute	Value
Высота H	36,00 mm
Номинальный диаметр dn	6,00 mm
Резьба G1	G1/4"-F
Длина резьбы LG1	15,0 mm
Размер гаечного ключа SW1	22,0 mm
Ход пружины Z	10,6 mm
Диаметр Ds	63,5 mm
Диаметр Dmax(S)	70,5 mm

Конструктивные данные SAG 60 NBR-60 G1/4-IG



Art.-Nr.: 10.01.01.12267



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	60,0 Shore A
Внутренний диаметр шланга (реком.) d	6,0 mm
Радиус заготовки мин. (выпуклый)	50,0 mm
Всасывающая сила (-600 мбар)	122,00 N
Вес	44,9 g
Поперечная сила	153,0 N
Поперечная сила маслянистой поверхности	80,0 N
Объем	22,000 cm ³
размер	60,00
Количество складок	0,0
Семейство продуктов	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12267

