

Bell suction cup (oval)

SAOG-S 60x20 NBR-60 G3/8-IG


Art.-Nr.: 10.01.01.12253



Technical data

Attribute	Value
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60.0 Shore A
Connection	G3/8-IG
Dimension (LxW)	60x20
Nipple material	Nickel plated

SAOG-S 60x20 NBR-60 G3/8-IG



Design data

Attribute	Value
Height H	28.50 mm
Nominal diameter dn	6.00 mm
Thread G1	G3/8"-F
Thread length LG1	9.0 mm
Key width SW1	22.0 mm
Spring stroke Z	5.0 mm
Suction cup width Bs	20.90 mm
Ls	60.90 mm
Lmax.(S)	65.80 mm
Bmax(S)	25.80 mm

Design data SAOG-S 60x20 NBR-60 G3/8-IG



WWW.SCHMALZ.COM/10.01.01.12253

Art.-Nr.: 10.01.01.12253

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	12.5 mm
Suction force (-600mbar)	56.00 N
Weight	40.7 g
Dimension (LxW)	60 x 20
Lateral force	45.0 N
Lateral force oily surface	30.0 N
Volume	4.000 cm ³
Number of folds	0.0
Product family	SAOG-S

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12253

**Ordering Data Spare Parts 10.01.01.12253**

Typ		Item number
Sealing ring (f. screwing)	DR G1/8 13.8/10.2x1.5 AL	10.07.08.00094
Extension with hexagon	ERW-S G1/8-AG G3/8-IG	10.08.04.00077

