


Art.-Nr.: 10.01.01.12302



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	60,0 Shore A
Соединение	M10-AG
Размеры (ДхШ)	60x20
Материал ниппеля	Сталь

SAOG-S 60x20 NBR-60 M10-AG



Конструктивные данные

Attribute	Value
Высота H	32,50 mm
Номинальный диаметр dn	5,10 mm
Резьба G1	M10-M
Длина резьбы LG1	10,0 mm
Размер гаечного ключа SW1	16,0 mm
Ход пружины Z	5,0 mm
Ширина присоски Bs	20,90 mm
Ls	60,90 mm
Lмакс.(S)	65,80 mm
Bмакс.(S)	25,80 mm

Конструктивные данные SAOG-S 60x20 NBR-60 M10-AG



Art.-Nr.: 10.01.01.12302



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Внутренний диаметр шланга (реком.) d	4,0 mm
Радиус заготовки мин. (выпуклый)	12,5 mm
Всасывающая сила (-600 мбар)	56,00 N
Вес	26,5 g
Размеры (ДхШ)	60 x 20
Поперечная сила	45,0 N
Поперечная сила маслянистой поверхности	30,0 N
Объем	4,000 cm ³
Количество складок	0,0
Семейство продуктов	SAOG-S

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12302

