


Art.-Nr.: 10.01.01.12301



SAG 80 NBR-60 M10-AG

Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	60,0 Shore A
размер	80,00
Соединение	M10-AG
Материал ниппеля	Сталь



Конструктивные данные

Attribute	Value
Высота H	35,00 mm
Номинальный диаметр dn	4,00 mm
Резьба G1	M10-M
Длина резьбы LG1	12,0 mm
Размер гаечного ключа SW1	22,0 mm
Ход пружины Z	12,8 mm
Диаметр Ds	83,0 mm
Диаметр Dmax(S)	90,7 mm

Конструктивные данные SAG 80 NBR-60 M10-AG



Art.-Nr.: 10.01.01.12301



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	60,0 Shore A
Всасывающая сила (-600 мбар)	217,00 N
Вес	68,6 g
размер	80,00
Количество складок	0,0
Семейство продуктов	SAG

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12301

