


Art.-Nr.: 10.01.01.12303



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	60,0 Shore A
Соединение	M10-AG
Размеры (ДхШ)	80x30
Материал ниппеля	Сталь

SAOG-S 80x30 NBR-60 M10-AG



Конструктивные данные

Attribute	Value
Высота H	33,50 mm
Номинальный диаметр dn	4,00 mm
Резьба G1	M10-M
Длина резьбы LG1	10,0 mm
Размер гаечного ключа SW1	16,0 mm
Ход пружины Z	6,0 mm
Ширина присоски Bs	30,90 mm
Ls	80,90 mm
Lmax.(S)	86,50 mm
Bmax(S)	37,50 mm

Конструктивные данные SAOG-S 80x30 NBR-60 M10-AG



Art.-Nr.: 10.01.01.12303



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Внутренний диаметр шланга (реком.) d	4,0 mm
Радиус заготовки мин. (выпуклый)	20,0 mm
Всасывающая сила (-600 мбар)	105,00 N
Вес	34,1 g
Размеры (ДхШ)	80 x 30
Поперечная сила	130,0 N
Поперечная сила маслянистой поверхности	91,0 N
Объем	11,000 cm ³
Количество складок	0,0
Семейство продуктов	SAOG-S

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12303

