


Art.-Nr.: 10.01.01.12360

**Технические данные**

Attribute	Value
Материал присоски	Высокотемпературный материал HT2
Твердость материала [Shore A]	65,0 Shore A
размер	60,00
Термостойкость	200,0 °C
Соединение	G1/4-IG
Материал ниппеля	никелированный

SAF 60 HT2-65 G1/4-IG

Присоска SAF HT2, доступная в различных диаметрах, доставляется с соединительным ниппелем, вулканизированным в эластомерную часть.

**Конструктивные данные**

Attribute	Value
Высота H	36,00 mm
Номинальный диаметр dn	6,00 mm
Резьба G1	G1/4"-F
Длина резьбы LG1	15,0 mm
Размер гаечного ключа SW1	22,0 mm
Ход пружины Z	6,0 mm
Диаметр Ds	60,6 mm
Диаметр Dmax(S)	67,0 mm

Конструктивные данные SAF 60 HT2-65 G1/4-IG



Art.-Nr.: 10.01.01.12360



Технические данные

Attribute	Value
Всасывающая сила (-600 мбар)	150,00 N
размер	60,00
Термостойкость	200,0 °C
Количество складок	0,0
Семейство продуктов	SAF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12360

Данные для заказа Аксессуары **10.01.01.12360**

Тип		Количество предметов
Чехол присоски	SU 60	10.01.01.13585

