




Технические данные

Attribute	Value
Материал присоски	Высокотемпературный материал HT2
Твердость материала [Shore A]	65,0 Shore A
размер	50,00
Термостойкость	200,0 °C
Соединение	G3/8-IG
Материал ниппеля	алюминий

SAF 50 HT2-65 G3/8-IG

Присоска SAF HT2, доступная в различных диаметрах, доставляется с соединительным ниппелем, вулканизированным в эластомерную часть.



Конструктивные данные

Attribute	Value
Высота H	28,00 mm
Номинальный диаметр dn	6,00 mm
Резьба G1	G3/8"-F
Длина резьбы LG1	15,0 mm
Размер гаечного ключа SW1	22,0 mm
Ход пружины Z	5,0 mm
Диаметр Ds	50,0 mm
Диаметр Dmax(S)	56,0 mm

Конструктивные данные SAF 50 HT2-65 G3/8-IG

Art.-Nr.: 10.01.01.12358



Технические данные

Attribute	Value
Всасывающая сила (-600 мбар)	100,00 N
размер	50,00
Термостойкость	200,0 °C
Количество складок	0,0
Семейство продуктов	SAF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12358

Данные для заказа Аксессуары **10.01.01.12358**

Тип		Количество предметов
Чехол присоски	SU 50	10.01.01.12837

