

Плоская присоска (круглая)

SGP 30 HT1-60 N033




Art.-Nr.: 10.01.01.12395



Технические данные

Attribute	Value
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60.0 Shore A
размер	30.00
Свойство материала	немаркий

SGP 30 HT1-60 N033



Конструктивные данные

Attribute	Value
Высота H2	15.70 mm
Высота H	22.20 mm
Диаметр головки Dk	15.6 mm
Внутренний диаметр d	11.20 mm
Ход пружины Z	2.0 mm
Диаметр Ds	30.0 mm
Диаметр Dmax(S)	32.0 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные SGP 30 HT1-60 N033



WWW.SCHMALZ.COM/10.01.01.12395

1

Плоская присоска (круглая)

SGP 30 HT1-60 N033



Art.-Nr.: 10.01.01.12395



Технические данные

Attribute	Value
Семейство ниппелей	N 033
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60.0 Shore A
Всасывающая сила (-600 мбар)	19.00 N
Вес	3.1 g
Объем	3.000 cm ³
размер	30.00
Количество складок	0.0
Семейство продуктов	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12395



WWW.SCHMALZ.COM/10.01.01.12395