


Düz vantuz (yuvarlak)

SGP 30 HT1-60 N033




Art.-Nr.: 10.01.01.12395



SGP 30 HT1-60 N033

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyut	30.00
Malzeme özelliği	iz bırakmayan



Tasarım verileri SGP 30 HT1-60 N033

Tasarım verileri

Attribute	Value
Yükseklik H2	15.70 mm
Yükseklik H	22.20 mm
Kafa çapı Dk	15.6 mm
İç çap d	11.20 mm
Yay stroku Z	2.0 mm
Çap Ds	30.0 mm
Çap Dmax(S)	32.0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.12395

Düz vantuz (yuvarlak)

SGP 30 HT1-60 N033



Art.-Nr.: 10.01.01.12395



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 033
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Emme kuvveti (-600mbar)	19.00 N
Ağırlık	3.1 g
Cilt	3.000 cm ³
Boyut	30.00
Körük Sayısı	0.0
Ürün ailesi	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12395



WWW.SCHMALZ.COM/10.01.01.12395