


Art.-Nr.: 10.01.01.12458



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	60,0 Shore A
Размеры (ДxШ)	70 x 25
Соединение	G1/4-AG
Материал ниппеля	алюминий

SAOK 70x25 NBR-60 G1/4-AG



Конструктивные данные

Attribute	Value
Высота H	27,50 mm
Номинальный диаметр dn	5,00 mm
Резьба G1	G1/4"-M
Длина резьбы LG1	8,0 mm
Размер гаечного ключа SW1	17,0 mm
Ход пружины Z	12,8 mm
Ширина присоски Bs	22,60 mm
Ls	67,20 mm
Lмакс.(S)	71,00 mm

Конструктивные данные SAOK 70x25 NBR-60 G1/4-AG



Art.-Nr.: 10.01.01.12458



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Внутренний диаметр шланга (реком.) d	6,0 mm
Сила отрыва	81,00 N
Вес	27,3 g
Размеры (ДхШ)	70 x 25
Поперечная сила	46,0 N
Поперечная сила маслянистой поверхности	20,0 N
Количество складок	0,0
Сила отрыва маслянистой поверхности	60,00 N
Угол заготовки W мин.	80,0 °
Семейство продуктов	SAOK

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12458

