


Плоская присоска (круглая)
SGP 35 SI-50 N034



Art.-Nr.: 10.01.01.12784



SGP 35 SI-50 N034



Конструктивные данные SGP 35 SI-50 N034

Технические данные

Attribute	Value
Материал присоски	Силикон SI
Твердость материала [Shore A]	50,0 Shore A
размер	35,00

Конструктивные данные

Attribute	Value
Высота H2	14,80 mm
Высота H	23,50 mm
Диаметр головки Dk	16,5 mm
Внутренний диаметр d	10,00 mm
Ход пружины Z	0,5 mm
Диаметр Ds	30,2 mm
Диаметр Dmax(S)	35,0 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.01.12784

1

Плоская присоска (круглая)
SGP 35 SI-50 N034



Art.-Nr.: 10.01.01.12784



Технические данные

Attribute	Value
Семейство ниппелей	N 034
Материал присоски	Силикон SI
Твердость материала [Shore A]	50,0 Shore A
Всасывающая сила (-600 мбар)	31,00 N
Вес	6,4 g
Объем	2,800 cm ³
размер	35,00
Количество складок	0,0
Семейство продуктов	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12784



WWW.SCHMALZ.COM/10.01.01.12784

2