


SGP 35 HT1-60 N034

Технические данные

Attribute	Value
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60.0 Shore A
размер	35.00



Конструктивные данные SGP 35 HT1-60 N034

Конструктивные данные

Attribute	Value
Высота H2	14.80 mm
Высота H	23.50 mm
Диаметр головки Dk	16.5 mm
Внутренний диаметр d	10.00 mm
Ход пружины Z	0.5 mm
Диаметр Ds	30.2 mm
Диаметр Dmax(S)	35.0 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Art.-Nr.: 10.01.01.12811



Технические данные

Attribute	Value
Семейство ниппелей	N 034
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60.0 Shore A
Всасывающая сила (-600 мбар)	31.00 N
Вес	6.4 g
Объем	2.800 cm ³
размер	35.00
Количество складок	0.0
Семейство продуктов	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12811

