

Art.-Nr.: 10.01.01.12651



Technical data


Attribute	Value
Material	Aluminum
Shape	High flow
Compressed air connection	M5-F
Diameter	30.0 mm

SBS 30 HF M5-IG AL

Floating suction cup SBS is delivered assembled. The assembly consists of:

- Floating suction cup of type SBS – available in various diameters
- Elastomer buffer made of the material HT1
- Optional product addition: central support

Available spare parts: Elastomer buffer, friction ring



Design data

Attribute	Value
Width B	32.00 mm
Height H1	17.50 mm
Height H	17.00 mm
Outside diameter D	30.00 mm
Thread G1	M5-F
Thread length LG1	5.0 mm
Thread G2	M4-F
Thread length LG2	6.0 mm
Thread length LG3	6.0 mm
Hole spacing X1	22.0 mm

Design data SBS 30 HF M5-IG AL



Art.-Nr.: 10.01.01.12651




Technical data

Attribute	Value
Weight	30.5 g
Air consumption [l/min]	140.0 l/min
Air consumption	8.400 m³/h
Holding force	5.0 N
Pressure range (operating pressure) [bar]	1.0 ... 6.0 bar
Product family	SBS


Note: Air consumption: The values provided are based on an operating pressure of 5 bar, measured on a suction-tight workpiece. The actual values may differ depending on the properties of the workpiece.



Performance data



Air consumption



Holding force



Air consumption

Typ	2	3	4	5	6
SBS 20...40 HF	65	85	110	140	170
SBS 60 HF	110	150	180	220	250
SBS 100/120 HF	205	280	350	420	490

Art.-Nr.: 10.01.01.12651



Holding force

Typ	1	2	3	4	5	6
SBS 20 HF	0.50	1.00	2.00	2.70	3.30	4.00
SBS 30 HF	1.00	2.30	3.00	4.00	5.00	5.50
SBS 40 HF	3.00	5.10	7.80	10.00	11.00	12.00



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12651



Ordering Data Spare Parts 10.01.01.12651

Typ	Item number
Friction surface (f. spec. grippers)	REIB-FL SBS HT1-60 10.01.01.12585

