



Art.-Nr.: 10.01.01.12812



SGP 40 HT1-60 N035



Конструктивные данные SGP 40 HT1-60 N035

Технические данные

Attribute	Value
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60.0 Shore A
размер	40.00

Конструктивные данные

Attribute	Value
Высота H2	14.50 mm
Высота H	20.60 mm
Диаметр головки Dk	16.0 mm
Внутренний диаметр d	8.00 mm
Ход пружины Z	2.3 mm
Диаметр Ds	40.0 mm
Диаметр Dmax(S)	42.0 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Art.-Nr.: 10.01.01.12812



Технические данные

Attribute	Value
Семейство ниппелей	N 035
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60.0 Shore A
Всасывающая сила (-600 мбар)	33.00 N
Вес	5.2 g
Объем	3.800 cm ³
размер	40.00
Количество складок	0.0
Семейство продуктов	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12812

