


Düz vantuz (yuvarlak)

SGP 40 HT1-60 N035




Art.-Nr.: 10.01.01.12812



SGP 40 HT1-60 N035

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyut	40,00



Tasarım verileri

Attribute	Value
Yükseklik H2	14,50 mm
Yükseklik H	20,60 mm
Kafa çapı Dk	16,0 mm
İç çap d	8,00 mm
Yay stroku Z	2,3 mm
Çap Ds	40,0 mm
Çap Dmax(S)	42,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Tasarım verileri SGP 40 HT1-60 N035



WWW.SCHMALZ.COM/10.01.01.12812

Düz vantuz (yuvarlak)

SGP 40 HT1-60 N035



Art.-Nr.: 10.01.01.12812



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 035
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Emme kuvveti (-600mbar)	33,00 N
Ağırlık	5,20 g
Cilt	3,800 cm ³
Boyut	40,00
Körük Sayısı	0,0
Ürün ailesi	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12812



WWW.SCHMALZ.COM/10.01.01.12812