

Плоская присоска (круглая)
SGP 34 FPM-65 N033


Art.-Nr.: 10.01.01.12919



SGP 34 FPM-65 N033

Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM
Твердость материала [Shore A]	65,0 Shore A
размер	34,00



Конструктивные данные SGP 34 FPM-65 N033

Конструктивные данные

Attribute	Value
Высота H2	16,80 mm
Высота H	23,00 mm
Диаметр головки Dk	15,2 mm
Внутренний диаметр d	11,20 mm
Ход пружины Z	2,2 mm
Диаметр Ds	34,0 mm
Диаметр Dmax(S)	37,5 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.01.12919

Плоская присоска (круглая)
SGP 34 FPM-65 N033



Art.-Nr.: 10.01.01.12919



Технические данные

Attribute	Value
Семейство ниппелей	N 033
Материал присоски	Фторкаучук FPM
Твердость материала [Shore A]	65,0 Shore A
Всасывающая сила (-600 мбар)	25,00 N
Вес	5,6 g
Объем	3,700 cm ³
размер	34,00
Количество складок	0,0
Семейство продуктов	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12919



WWW.SCHMALZ.COM/10.01.01.12919

2