

Art.-Nr.: 10.01.01.12922



Technical data


Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Size	20.00
Vacuum connection	G 1/8"-M
Nipple material	Aluminum

SGPN 20 FPM-65 G1/8-AG

Flat suction cup SGPN (elastomer part + connection nipple) is delivered unassembled. The delivery consists of:

- Suction cup of type SGP – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup SGP, connection nipple SA-NIP



Design data

Height H	16.40 mm
Nominal diameter dn	3.50 mm
Thread G1	G 1/8"-M
Thread length LG1	7.5 mm
Key width SW1	14.0 mm
Spring stroke Z	1.5 mm
Diameter Ds	20.0 mm
Diameter Dmax(S)	22.0 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data SGPN 20 FPM-65 G1/8-AG



Art.-Nr.: 10.01.01.12922

**Technical data**

Suction cup material	Fluorine rubber FPM
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Suction force (-600mbar)	8.50 N
Weight	5.60 g
Volume	0.310 cm ³
Size	20.00
Number of folds	0.0
Product family	SGPN

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Ordering Data Spare Parts 10.01.01.12922**

Typ		Item number
Suction Cup Connection Nipples	SA-NIP N016 G1/8-AG DN350	10.01.06.05735

**Ordering Data Wear Parts 10.01.01.12922**

Typ		Item number
Flat suction cup (round)	SGP 20 FPM-65 N016	10.01.01.12909

