


Art.-Nr.: 10.01.01.12908



SGP 15 FPM-65 N016



Конструктивные данные SGP 15 FPM-65 N016

Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM
Твердость материала [Shore A]	65.0 Shore A
размер	15.00
Свойство материала	немаркий

Конструктивные данные

Attribute	Value
Высота H2	7.20 mm
Высота H	10.00 mm
Диаметр головки Dk	9.5 mm
Внутренний диаметр d	4.50 mm
Ход пружины Z	0.9 mm
Диаметр Ds	14.5 mm
Диаметр Dmax(S)	15.5 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Art.-Nr.: 10.01.01.12908



Технические данные

Attribute	Value
Семейство ниппелей	N 016
Материал присоски	Фторкаучук FPM
Твердость материала [Shore A]	65.0 Shore A
Всасывающая сила (-600 мбар)	5.50 N
Вес	0.7 g
Объем	0.278 cm ³
размер	15.00
Количество складок	0.0
Семейство продуктов	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12908

