

Düz vantuz (yuvarlak)

SGP 15 FPM-65 N016


Art.-Nr.: 10.01.01.12908



SGP 15 FPM-65 N016

Teknik veriler

Attribute	Value
Vantuz malzemesi	Fluorocaotchuc FPM
Malzeme sertliği [Shore A]	65.0 Shore A
Boyut	15.00
Malzeme özelliği	iz bırakmayan



Tasarım verileri SGP 15 FPM-65 N016

Tasarım verileri

Attribute	Value
Yükseklik H2	7.20 mm
Yükseklik H	10.00 mm
Kafa çapı Dk	9.5 mm
İç çap d	4.50 mm
Yay stroku Z	0.9 mm
Çap Ds	14.5 mm
Çap Dmax(S)	15.5 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.12908

Düz vantuz (yuvarlak)

SGP 15 FPM-65 N016



Art.-Nr.: 10.01.01.12908



Teknik veriler

Attribute	Value
Meme ucu ailesi	N 016
Vantuz malzemesi	Fluorocaotchuc FPM
Malzeme sertliği [Shore A]	65.0 Shore A
Emme kuvveti (-600mbar)	5.50 N
Ağırlık	0.7 g
Cilt	0.278 cm ³
Boyut	15.00
Körük Sayısı	0.0
Ürün ailesi	SGP

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.12908



WWW.SCHMALZ.COM/10.01.01.12908