


Art.-Nr.: 10.01.01.13104



SPL 40 POM-NBR G1/8-IG

Присоска SPL POM-NBR доступна с различными диаметрами и поставляется в виде готового к подключению продукта.



Конструктивные данные SPL 40 POM-NBR G1/8-IG

Технические данные

Attribute	Value
Материал присоски	Полиоксиметилен пербунан POM-NBR
размер	40,00
Соединение	G1/8-IG

Конструктивные данные

Attribute	Value
Высота H	20,50 mm
Диаметр головки Dk	42,0 mm
Резьба G1	G1/8"-F
Длина резьбы LG1	9,5 mm
Размер гаечного ключа SW1	17,0 mm
Ход пружины Z	2,0 mm
Диаметр Ds	39,0 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3



Art.-Nr.: 10.01.01.13104



Технические данные

Attribute	Value
Материал присоски	Полиоксиметилен пербунан POM-NBR
Внутренний диаметр шланга (реком.) d	4,0 mm
Всасывающая сила (-600 мбар)	70,00 N
Вес	28,0 g
Объем	4,700 cm ³
Соединение	G1/8-IG
Семейство продуктов	SPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13104

