



SPL 40 POM-NBR G1/8-IG

Vakum plakası SPL POM-NBR farklı çaplarda mevcuttur ve bağlanmaya hazır bir ürün olarak teslim edilir.


## Teknik veriler

| Attribute        | Value                            |
|------------------|----------------------------------|
| Vantuz malzemesi | Polioksimetilen perbunan POM-NBR |
| Boyut            | 40.00                            |
| Bağlantı         | G1/8-IG                          |

## Tasarım verileri

| Attribute          | Value    |
|--------------------|----------|
| Yükseklik H        | 20.50 mm |
| Kafa çapı Dk       | 42.0 mm  |
| Diş G1             | G1/8"-F  |
| Diş uzunluğu LG1   | 9.5 mm   |
| Anahtar boyutu SW1 | 17.0 mm  |
| Yay stroku Z       | 2.0 mm   |
| Çap Ds             | 39.0 mm  |

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



Tasarım verileri SPL 40 POM-NBR G1/8-IG

Art.-Nr.: 10.01.01.13104



## Teknik veriler

| Attribute                      | Value                            |
|--------------------------------|----------------------------------|
| Vantuz malzemesi               | Polioksümetilen perbunan POM-NBR |
| Hortum çapı (tavsiye edilen) d | 4.0 mm                           |
| Emme kuvveti (-600mbar)        | 70.00 N                          |
| Ağırlık                        | 28.0 g                           |
| Cilt                           | 4.700 cm <sup>3</sup>            |
| Bağlantı                       | G1/8-IG                          |
| Ürün ailesi                    | SPL                              |

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



## Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.01.13104](http://www.schmalz.com/10.01.01.13104)

