


Art.-Nr.: 10.01.01.13107

**Технические данные**

Attribute	Value
Материал присоски	Полиоксиметилен пербунан POM-NBR
размер	70,00
Соединение	G1/4-IG

SPL 70 POM-NBR G1/4-IG

Присоска SPL POM-NBR доступна с различными диаметрами и поставляется в виде готового к подключению продукта.

**Конструктивные данные**

Attribute	Value
Высота H	24,50 mm
Диаметр головки Dk	73,0 mm
Резьба G1	G1/4"-F
Длина резьбы LG1	11,5 mm
Размер гаечного ключа SW1	22,0 mm
Ход пружины Z	3,0 mm
Диаметр Ds	68,0 mm

Примечание: Допустимые допуски размеров для деталей из эластомера в соответствии с DIN ISO 3302-1 M3

Конструктивные данные SPL 70 POM-NBR G1/4-IG



Art.-Nr.: 10.01.01.13107



Технические данные

Attribute	Value
Материал присоски	Полиоксиметилен пербунан POM-NBR
Внутренний диаметр шланга (реком.) d	6,0 mm
Всасывающая сила (-600 мбар)	217,00 N
Вес	91,0 g
Объем	24,100 cm ³
Соединение	G1/4-IG
Семейство продуктов	SPL

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13107

Данные для заказа Запасные части **10.01.01.13107**

Тип	Количество предметов
V-ринг	V-RING 63x13 V-65 S NBR 10.07.08.00100

