

SPF 30 ED-65 G1/8-IG

Technical data


Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	65.0 Shore A
Size	30.00
Thread G1	G1/8"-F

Suction cup SPF (elastomer part + connection element) is delivered assembled. The assembly consists of:

- Suction cup of type SPF – elastomer part, available in various diameters
- Connection element of type SC – available with various threads

Available spare parts: suction cup SPF, Schmalz-Connector

Available accessories: filter screen (sieve, round)



Design data SPF 30 ED-65 G1/8-IG

Design data

Attribute	Value
Height H	26.00 mm
Nominal diameter dn	4.10 mm
Thread G1	G1/8"-F
Thread length LG1	8.0 mm
Key width SW1	14.0 mm
Spring stroke Z	2.5 mm
Diameter Ds	31.4 mm
Diameter Dmax(S)	33.6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Art.-Nr.: 10.01.01.13245

**Technical data**

Attribute	Value
Suction cup material	Elastodur ED
Material hardness [Shore A]	65.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	35.0 mm
Pull-off force	35.30 N
Suction force (-600mbar)	29.50 N
Weight	7.8 g
Lateral force	22.5 N
Volume	2.531 cm ³
Size	30.00
Number of folds	0.0
Product family	SPF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13245

**Ordering Data Accessories 10.01.01.13245**

Typ		Item number
Sieve, round	SIEB 11x1 MS-A2 280 0.28/0.16	10.07.01.00309
Suction cup cover	SU 30	10.01.01.12889

**Ordering Data Spare Parts 10.01.01.13245**

Typ		Item number
Schmalz-Connector	SC 040 G1/8-IG	10.01.06.02482

**Ordering Data Wear Parts 10.01.01.13245**

Typ		Item number
Flat suction cup (round)	SPF 30 ED-65 SC040	10.01.01.12372

