




SPL-HT 120 FPM-F-65

Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM-F
Твердость материала [Shore A]	65.0 Shore A
размер	120.00
Рабочая температура макс.	350.0 °C



Конструктивные данные SPL-HT 120 FPM-F-65

Конструктивные данные

Attribute	Value
Высота H2	5.00 mm
Высота H	43.00 mm
Диаметр головки Dk	105.0 mm
Внутренний диаметр d1	96.0 mm
d2	4.0 mm
Внутренний диаметр d	88.00 mm
Ход пружины Z	25.0 mm
Диаметр Ds	120.0 mm
Высота H3	10.00 mm
Диаметр Dmax(S)	130.0 mm

Вакуумная плита (круглая)
SPL-HT 120 FPM-F-65



Art.-Nr.: 10.01.01.13435



Технические данные

Attribute	Value
Материал присоски	Фторкаучук FPM-F
Радиус заготовки мин. (выпуклый)	300.0 mm
Всасывающая сила (-600 мбар)	675.00 N
Вес	138.1 g
Объем	255.000 cm ³
размер	120.00
Рабочая температура макс.	350.0 °C
Семейство продуктов	SPL-HT

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.13435



WWW.SCHMALZ.COM/10.01.01.13435