



Art.-Nr.: 10.01.01.14044



SFF 10 EPDM-45 SC030

Технические данные

Attribute	Value
Материал присоски	EPDM
Твердость материала [Shore A]	45,0 Shore A
размер	10,00
Количество складок	0,0



Конструктивные данные

Attribute	Value
Высота H2	4,20 mm
Высота H	10,40 mm
Диаметр головки Dk	9,3 mm
Внутренний диаметр d1	7,3 mm
Внутренний диаметр d	5,50 mm
Ход пружины Z	0,7 mm
Диаметр Ds	10,0 mm
Высота H3	5,90 mm
Диаметр Dmax(S)	11,0 mm

Конструктивные данные SFF 10 EPDM-45 SC030



Art.-Nr.: 10.01.01.14044



Технические данные

Attribute	Value
Семейство ниппелей	SC 030
Материал присоски	EPDM
Твердость материала [Shore A]	45,0 Shore A
Радиус заготовки мин. (выпуклый)	8,0 mm
Сила отрыва	3,00 N
Всасывающая сила (-600 мбар)	2,70 N
Вес	0,4 g
Объем	0,245 cm ³
размер	10,00
Количество складок	0,0
Семейство продуктов	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14044

Данные для заказа Аксессуары **10.01.01.14044**

Тип	Количество предметов
Соединитель Schmalz SC 030 M5-AG	10.01.06.02802

