


SFF 10 HT1-60 SC030



Конструктивные данные SFF 10 HT1-60 SC030

Технические данные

Attribute	Value
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60.0 Shore A
размер	10.00
Количество складок	0.0

Конструктивные данные

Attribute	Value
Высота H2	4.20 mm
Высота H	10.40 mm
Диаметр головки Dk	9.3 mm
Внутренний диаметр d1	7.3 mm
Внутренний диаметр d	5.50 mm
Ход пружины Z	0.7 mm
Диаметр Ds	10.0 mm
Высота H3	5.90 mm
Диаметр Dmax(S)	11.0 mm

Art.-Nr.: 10.01.01.14050



Технические данные

Attribute	Value
Семейство ниппелей	SC 030
Материал присоски	Высокотемпературный материал HT1
Твердость материала [Shore A]	60.0 Shore A
Радиус заготовки мин. (выпуклый)	8.0 mm
Сила отрыва	3.00 N
Всасывающая сила (-600 мбар)	2.70 N
Вес	0.4 g
Объем	0.245 cm ³
размер	10.00
Количество складок	0.0
Семейство продуктов	SFF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14050

Заказать аксессуары для данных **10.01.01.14050**

Тип	Номер товара
Соединитель Schmalz	SC 030 M5-AG 10.01.06.02802

