




Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	55,0 Shore A
размер	90,00
Вакуумное соединение	G1/4"-M

SUF 90 NBR-55 G1/4-AG

Присоска SUF (эластомер+соединительный ниппель) поставляется собранной.

Доступные запасные части: присоска SUF, соединительный ниппель SC



Конструктивные данные

Attribute	Value
Высота H	23,20 mm
Номинальный диаметр dn	5,10 mm
Резьба G1	G1/4"-M
Длина резьбы LG1	10,0 mm
Размер гаечного ключа SW1	17,0 mm
Ход пружины Z	7,0 mm
Диаметр Ds	90,0 mm
Диаметр Dmax(S)	98,1 mm

Конструктивные данные SUF 90 NBR-55 G1/4-AG



Art.-Nr.: 10.01.01.14060



Технические данные

Attribute	Value
Материал присоски	Нитрильный каучук NBR
Твердость материала [Shore A]	55,0 Shore A
Внутренний диаметр шланга (реком.) d	6,0 mm
Радиус заготовки мин. (выпуклый)	150,0 mm
Сила отрыва	328,00 N
Всасывающая сила (-600 мбар)	328,00 N
Вес	98,1 g
Объем	34,300 cm ³
размер	90,00
Количество складок	0,0
Семейство продуктов	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14060

