

Flat suction cup (round)

SUF 80 SI-55 G1/4-AG



Art.-Nr.: 10.01.01.14069




Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Size	80.00
Vacuum connection	G1/4"-M
Material characteristics	FDA-compatible

SUF 80 SI-55 G1/4-AG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data

Height H	23.00 mm
Nominal diameter dn	5.10 mm
Thread G1	G1/4"-M
Thread length LG1	10.0 mm
Key width SW1	17.0 mm
Spring stroke Z	6.5 mm
Diameter Ds	80.0 mm
Diameter Dmax(S)	87.1 mm

Design data SUF 80 SI-55 G1/4-AG



WWW.SCHMALZ.COM/10.01.01.14069

1

Flat suction cup (round)

SUF 80 SI-55 G1/4-AG



Art.-Nr.: 10.01.01.14069



Technical data

Suction cup material	Silicone SI
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	100.0 mm
Pull-off force	254.00 N
Suction force (-600mbar)	254.00 N
Weight	71.10 g
Volume	25.100 cm ³
Size	80.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



WWW.SCHMALZ.COM/10.01.01.14069