

Flat suction cup (round)

## SUF 70 HT1-60 G1/4-IG



Art.-Nr.: 10.01.01.14083




### Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	70.00
Vacuum connection	G 1/4"-F

SUF 70 HT1-60 G1/4-IG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



### Design data

Height H	34.40 mm
Nominal diameter dn	5.10 mm
Thread G1	G 1/4"-F
Thread length LG1	12.0 mm
Key width SW1	17.0 mm
Spring stroke Z	6.0 mm
Diameter Ds	70.0 mm
Diameter Dmax(S)	77.2 mm

Design data SUF 70 HT1-60 G1/4-IG



[WWW.SCHMALZ.COM/10.01.01.14083](http://WWW.SCHMALZ.COM/10.01.01.14083)

1

Flat suction cup (round)

## SUF 70 HT1-60 G1/4-IG



Art.-Nr.: 10.01.01.14083



### Technical data

Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	100.0 mm
Pull-off force	198.00 N
Suction force (-600mbar)	198.00 N
Weight	61.30 g
Volume	18.000 cm <sup>3</sup>
Size	70.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



[WWW.SCHMALZ.COM/10.01.01.14083](http://WWW.SCHMALZ.COM/10.01.01.14083)