


Art.-Nr.: 10.01.01.14368

**Technical data**


Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Size	1.00
Vacuum connection	M3-M
Nipple material	Aluminum

PFYN 1 NBR-ESD-55 M3-AG

Suction cup PFYN (elastomer part + connection nipple) is delivered unassembled (diameters of 120 mm and more are assembled). The delivery consists of:

- Suction cup of type PFG – elastomer part, available in various diameters and materials
- Connection nipple of type SA-NIP – available with various threads

Available spare parts: suction cup PFG, connection nipple SA-NIP

**Design data**

Attribute	Value
Height H	3.60 mm
Nominal diameter dn	0.40 mm
Thread G1	M3-M
Thread length LG1	3.0 mm
Key width SW1	5.0 mm
Spring stroke Z	0.1 mm
Diameter Ds	1.0 mm
Diameter Dmax(S)	1.2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Design data PFYN 1 NBR-ESD-55 M3-AG



Art.-Nr.: 10.01.01.14368

**Technical data**

Attribute	Value
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55.0 Shore A
Hose inner diameter (recom.) d	2.0 mm
Workpiece radius min. (convex)	2.0 mm
Suction force (-600mbar)	0.03 N
Weight	1.0 g
Volume	0.001 cm ³
Size	1.00
Number of folds	0.0
Product family	PFYN

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14368

**Ordering Data Spare Parts 10.01.01.14368**

Typ		Item number
Flat suction cup (round)	PFG 1 NBR-ESD-55 N001	10.01.01.14345
Suction cup connection nipple	SA-NIP N001 M3-AG DN40	10.01.01.00315

