


Düz vantuz (yuvarlak)

SHF 50 NK-45 M10x1.25-IG E

Art.-Nr.: 10.01.01.14387



SHF 50 NK-45 M10x1.25-IG E



Tasarım verileri SHF 50 NK-45 M10x1.25-IG E

Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
Malzeme sertliği [Shore A]	45,0 Shore A
Boyut	50,00
Diş G1	M10x1.25-F
Tip	E

Tasarım verileri

Attribute	Value
Yükseklik H	17,90 mm
Kafa çapı Dk	36,8 mm
d2	29,7 mm
Diş G1	M10x1.25-F
Diş uzunluğu LG1	10,0 mm
Yay stroku Z	3,4 mm
Çap Ds	52,0 mm
Çap Dmax(S)	54,0 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.01.14387

Düz vantuz (yuvarlak)

SHF 50 NK-45 M10x1.25-IG E



Art.-Nr.: 10.01.01.14387



Teknik veriler

Attribute	Value
Vantuz malzemesi	Doğal Kauçuk NK
İş parçası yarıçapı dak (dışbükey)	50,0 mm
Emme kuvveti (-600mbar)	110,00 N
Ağırlık	21,00 g
Yanal kuvvet	90,0 N
Cilt	8,000 cm ³
Boyut	50,00
Emme kuvveti d2	40,00 N
Körük Sayısı	0,0
Ürün ailesi	SHF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14387



WWW.SCHMALZ.COM/10.01.01.14387