

Art.-Nr.: 10.01.01.14815



Technical data


Attribute	Value
Shape	High flow
Compressed air connection	G1/8"-F
Diameter	40.0 mm
Material	ESD/AL

SBS 40 HF G1/8-IG ESD/AL

The floating suction cup SBS-ESD is delivered assembled. The product consists of:

- Floating suction cup type SBS - available in various diameters
- Elastomer buffer made of NBR-ESD material
- Optional product addition: central support (SBS-40 and SBS-60)

Spare parts available: elastomer buffer, friction ring



Design data

Attribute	Value
Width B	41.00 mm
Height H1	17.40 mm
Height H	17.00 mm
Outside diameter D	40.00 mm
Thread G1	G1/8"-F
Thread length LG1	5.0 mm
Thread G2	M4-F
Thread length LG2	6.0 mm
Thread length LG3	6.0 mm
Hole spacing X1	32.0 mm


Design data SBS 40 HF G1/8-IG ESD/AL




Art.-Nr.: 10.01.01.14815

**Technical data**

Attribute	Value
Weight	51.0 g
Air consumption [l/min]	190.0 l/min
Air consumption	11.400 m³/h
Holding force	10.5 N
Pressure range (operating pressure) [bar]	1.0 ... 6.0 bar
Product family	SBS-ESD

**Performance data**

Air consumption



Holding force

**Air consumption**

Typ	2	3	4	5	6
SBS-ESD 20...40 HF	65	85	110	140	170
SBS-ESD 60 HF	110	150	180	220	250
SBS-ESD 100 HF	205	280	350	420	490

**Holding force**

Typ	1	2	3	4	5	6
SBS-ESD 20 HF	0.5	1	2.0	2.7	3.3	4.0
SBS-ESD 30 HF	1.0	2.3	3.0	4.0	5.0	5.5
SBS-ESD 40 HF	3.0	5.1	7.8	10.0	11.0	12.0



Floating suction cup

SBS 40 HF G1/8-IG ESD/AL



Art.-Nr.: 10.01.01.14815



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14815



Ordering Data Spare Parts 10.01.01.14815

Typ		Item number
Friction surface (f. spec. grippers)	REIB-FL SBS NBR-ESD-55	10.01.01.14382



WWW.SCHMALZ.COM/10.01.01.14815