

Art.-Nr.: 10.01.01.14820



Technical data


Attribute	Value
Shape	Standard flow
Compressed air connection	G1/8"-F
Diameter	60.0 mm
Additional function	Central Support
Material	NBR-ESD/AL

SBS 60 SF G1/8-IG CS NBR-ESD/AL

The floating suction cup SBS-ESD is delivered assembled. The product consists of:

- Floating suction cup type SBS - available in various diameters
- Elastomer buffer made of NBR-ESD material
- Optional product addition: central support (SBS-40 and SBS-60)

Spare parts available: elastomer buffer, friction ring



Design data SBS 60 SF G1/8-IG CS NBR-ESD/AL

Design data


Attribute	Value
Width B	61.60 mm
Height H1	17.40 mm
Height H	17.00 mm
Outside diameter D	60.00 mm
Thread G1	G1/8"-F
Thread length LG1	5.0 mm
Thread G2	M4-F
Thread length LG2	6.0 mm
Thread length LG3	6.0 mm
Hole spacing X1	45.0 mm
Thread G3	G1/8"-F



Art.-Nr.: 10.01.01.14820

**Technical data**

Attribute	Value
Weight	120.00 g
Air consumption [l/min]	150.0 l/min
Air consumption	9.000 m³/h
Holding force	13.0 N
Pressure range (operating pressure) [bar]	1.0 ... 6.0 bar
Product family	SBS-ESD

**Performance data**

Air consumption

**Air consumption**

Typ	2	3	4	5	6
SBS-ESD 10 SF	39.50	53.50	67.50	81.50	96.50
SBS-ESD 20...40 SF	50.00	70.00	85.00	100.00	125.00
SBS-ESD 60 SF	80.00	105.00	130.00	150.00	175.00
SBS-ESD 100 SF	110.00	150.00	190.00	225.00	260.00

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.14820WWW.SCHMALZ.COM/10.01.01.14820

Floating suction cup

SBS 60 SF G1/8-IG CS NBR-ESD/AL



Art.-Nr.: 10.01.01.14820



Ordering Data Spare Parts 10.01.01.14820

Typ		Item number
Friction surface (f. spec. grippers)	REIB-FL SBS NBR-ESD-55	10.01.01.14382
Friction surface (f. spec. grippers)	REIB-FL SBS NBR-ESD-55	10.01.01.14819



WWW.SCHMALZ.COM/10.01.01.14820