




SUF 15 HT1-60 NPT1/8-IG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data SUF 15 HT1-60 NPT1/8-IG

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	15.00
Vacuum connection	NPT1/8-F

Design data

Attribute	Value
Height H	22.90 mm
Nominal diameter dn	3.10 mm
Thread G1	NPT1/8"-F
Thread length LG1	9.5 mm
Key width SW1	14.0 mm
Spring stroke Z	1.5 mm
Diameter Ds	15.0 mm
Diameter Dmax(S)	16.8 mm

Art.-Nr.: 10.01.01.15009

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	4.0 mm
Workpiece radius min. (convex)	20.0 mm
Pull-off force	9.00 N
Weight	5.70 g
Volume	0.220 cm ³
Size	15.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.15009

**Ordering Data Spare Parts 10.01.01.15009**

Typ		Item number
Schmalz-Connector	SC 030 NPT1/8-IG	10.01.06.04895
Flat suction cup (round)	SUF 15 HT1-60 SC030	10.01.01.13989

