


Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Size	80.00
Vacuum connection	NPT1/4-M

SUF 80 HT1-60 NPT1/4-AG

Suction cup SUF (elastomer part + connector) is delivered assembled.

Available spare parts: suction cup SUF, connector SC



Design data

Attribute	Value
Height H	23.00 mm
Nominal diameter dn	5.50 mm
Thread G1	NPT1/4" -M
Thread length LG1	16.0 mm
Key width SW1	22.0 mm
Spring stroke Z	6.5 mm
Diameter Ds	80.0 mm
Diameter Dmax(S)	87.1 mm

Design data SUF 80 HT1-60 NPT1/4-AG

Art.-Nr.: 10.01.01.15154

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Hose inner diameter (recom.) d	6.0 mm
Workpiece radius min. (convex)	100.0 mm
Pull-off force	254.00 N
Suction force (-600mbar)	254.00 N
Weight	71.10 g
Volume	25.100 cm ³
Size	80.00
Number of folds	0.0
Product family	SUF

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.01.15154

**Ordering Data Spare Parts 10.01.01.15154**

Typ		Item number
Reduction nipple with hexagon	RED-NIP NPT1/4-AG AL	10.01.01.15181
Flat suction cup (round)	SUF 80 HT1-60 M10x1.25-IG N009	10.01.01.13999

