




FSTE G1/4-AG 75

Yaylı piston FSTE bağlanmaya hazır bir ürün olarak teslim edilir.



Tasarım verileri FSTE G1/4-AG 75

**Teknik veriler**

| Attribute               | Value   |
|-------------------------|---------|
| Yay stroku Z            | 75,0 mm |
| Vantuz bağlantısı       | G1/4"-M |
| Vakum bağlantısı        | G1/8"-F |
| Tightening torque (max) | 40,0 Nm |

**Tasarım verileri**

| Attribute          | Value     |
|--------------------|-----------|
| Yükseklik H2       | 99,50 mm  |
| Yükseklik H        | 145,00 mm |
| Diş G1             | G1/8"-F   |
| Diş uzunluğu LG1   | 13,0 mm   |
| Diş G2             | G1/4"-M   |
| Diş uzunluğu LG2   | 8,5 mm    |
| Diş uzunluğu LG3   | 40,0 mm   |
| Anahtar boyutu SW1 | 24,0 mm   |
| Anahtar boyutu SW2 | 17,0 mm   |
| Yay stroku Z       | 75,0 mm   |

Art.-Nr.: 10.01.02.00569

**Teknik veriler**

| Attribute               | Value       |
|-------------------------|-------------|
| Yay kuvveti merkezi     | 15,20 N     |
| Yay oranı               | 0,262 N/mm  |
| Yay ön gerilimi         | 5,38 N      |
| Yatay yük               | 340,0 N     |
| Dikey yük               | 2.400,0 N   |
| Ağırlık                 | 190,00 g    |
| Çalışma sıcaklığı       | 0 ... 80 °C |
| Ürün ailesi             | FSTE        |
| Tightening torque (max) | 40,0 Nm     |

Note: Spring force: Referred to 50 % of operating stroke Vertical loading: Maximum static loading Horizontal stress: The specification of the horizontal stress refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position

**Further documentation**

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.01.02.00569](http://www.schmalz.com/10.01.02.00569)

[WWW.SCHMALZ.COM/10.01.02.00569](http://WWW.SCHMALZ.COM/10.01.02.00569)

Art.-Nr.: 10.01.02.00569

**Sipariş Verisi Aksesuarlar 10.01.02.00569**

| Typ                     |                         | Ürün numarası  |
|-------------------------|-------------------------|----------------|
| Flexolink               | FLK G1/4-IG G1/4-AG     | 10.01.03.00178 |
| Bilyalı mafsal          | KGL G1/4-IG G1/4-AG     | 10.01.03.00110 |
| Bilyalı mafsal          | KGL G1/4-IG M10x1.25-AG | 10.01.03.00137 |
| Flexolink               | FLK G1/4-IG M10x1.25-AG | 10.01.03.00206 |
| Çapraz giriş bağlantısı | HTR-STA 55 1N D20 WI    | 10.08.03.00086 |
| Üniversal tutucu        | HTR-UNI 2N FSTE-HDB     | 10.01.03.00332 |
| Hortum manşonu          | ST G1/8-AG 4 M5-ROH     | 10.08.03.00153 |
| Hortum manşonu          | ST G1/8-AG 6 M5-V       | 10.08.03.00154 |
| Hortum manşonu          | ST G1/8-AG 9 M5-V       | 10.08.03.00155 |
| Otomatik rakor, düz     | STV-GE G1/8-AG 4        | 10.08.02.00202 |
| Otomatik rakor, düz     | STV-GE G1/8-AG 6        | 10.08.02.00204 |
| Otomatik rakor, düz     | STV-GE G1/8-AG 8        | 10.08.02.00206 |
| Tapa rakoru, dirsek     | STV-W G1/8-AG 4         | 10.08.02.00156 |
| Tapa rakoru, dirsek     | STV-W G1/8-AG 6         | 10.08.02.00158 |
| Tapa rakoru, dirsek     | STV-W G1/8-AG 8         | 10.08.02.00160 |
| Otomatik rakor, düz     | STV-GE G1/8-AG 6 HT     | 10.08.02.00389 |
| Tapa rakoru, dirsek     | STV-W G1/8-AG 6         | 10.08.02.00288 |
| Tapa rakoru, dirsek     | STV-W G1/8-AG 6 HT      | 10.08.02.00391 |
| Tapa rakoru, dirsek     | STV-WF G1/8-AG 4        | 10.08.02.00166 |
| Tapa rakoru, dirsek     | STV-WF G1/8-AG 6        | 10.08.02.00168 |
| Tapa rakoru, dirsek     | STV-WF G1/8-AG 8        | 10.08.02.00170 |
| Tapa rakoru, dirsek     | STV-WF G1/8-AG 10       | 10.08.02.00257 |
| Fiş birleşimi, T        | STV-T G1/8-AG 4         | 10.09.02.00039 |
| Fiş birleşimi, T        | STV-T G1/8-AG 6         | 10.09.02.00040 |
| Fiş birleşimi, T        | STV-T G1/8-AG 8         | 10.09.02.00041 |

**Sipariş Verisi Yedek Parça 10.01.02.00569**

| Typ         |                          | Ürün numarası  |
|-------------|--------------------------|----------------|
| Basınç yayı | DRUCK-FED 1x16 115 0.262 | 20.08.02.00061 |

