




SPLO 60x20 NBR-55 G1/8-IG

Çeşitli çaplarda ve isteğe bağlı olarak dokunmatik valfli olarak temin edilebilen vakum plakası SPLO, elastomer parçaya vulkanize edilmiş destek plakası ile birlikte teslim edilir.



Tasarım verileri SPLO 60x20 NBR-55 G1/8-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	60 x 20
Bağlantı	G1/8"-F
Yükseklik H	12.60 mm

Tasarım verileri

Attribute	Value
Yükseklik H2	6.00 mm
Yükseklik H	12.60 mm
Kafa uzunluğu Lk	75.00 mm
Diş G1	G1/8"-F
Diş uzunluğu LG1	6.0 mm
Delik boyutu d3	4.5 mm
Yay stroku Z	2.1 mm
Delik aralığı X1	65.0 mm
Vantuz genişliği Bs	19.00 mm
Ls	59.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Vakum plakası (oval)

SPLO 60x20 NBR-55 G1/8-IG



Art.-Nr.: 10.01.05.00001



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
İş parçası yarıçapı dak (dışbükey)	15.0 mm
Emme kuvveti (-600mbar)	50.00 N
Ağırlık	70.0 g
Boyutlar (LxW)	60 x 20
Cilt	3.222 cm ³
Körük Sayısı	0.0
Ürün ailesi	SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00001



WWW.SCHMALZ.COM/10.01.05.00001