




SPLO 100x32 NBR-55 G1/4-IG

Çeşitli çaplarda ve isteğe bağlı olarak dokunmatik valfli olarak temin edilebilen vakum plakası SPLO, elastomer parçaya vulkanize edilmiş destek plakası ile birlikte teslim edilir.



Tasarım verileri SPLO 100x32 NBR-55 G1/4-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	100 x 32
Bağlantı	G1/4"-F
Yükseklik H	14.00 mm

Tasarım verileri

Attribute	Value
Yükseklik H2	6.00 mm
Yükseklik H	14.00 mm
Kafa uzunluğu Lk	125.80 mm
Diş G1	G1/4"-F
Diş uzunluğu LG1	6.0 mm
Delik boyutu d3	5.3 mm
Yay stroku Z	2.0 mm
Delik aralığı X1	112.0 mm
Vantuz genişliği Bs	32.00 mm
Ls	100.00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları

Art.-Nr.: 10.01.05.00002



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
İş parçası yarıçapı dak (dışbükey)	50.0 mm
Emme kuvveti (-600mbar)	134.00 N
Ağırlık	180.0 g
Boyutlar (LxW)	100 x 32
Cilt	10.734 cm ³
Körük Sayısı	0.0
Ürün ailesi	SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and even workpiece surface - they do not include a safety factor



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00002

