

Düz vantuz (oval)

SGO 30x10 NBR-55 N022


Art.-Nr.: 10.01.05.00152



SGO 30x10 NBR-55 N022

Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Boyutlar (LxW)	30 x 10



Tasarım verileri SGO 30x10 NBR-55 N022

Tasarım verileri

Attribute	Value
Yükseklik H2	3.00 mm
Yükseklik H	12.00 mm
Kafa çapı Dk	11.5 mm
Nominal çap dn	2.50 mm
İç çap d1	7.0 mm
İç çap d	5.50 mm
Yay stroku Z	1.5 mm
Yükseklik H3	5.50 mm
Vantuz genişliği Bs	9.40 mm
Ls	29.40 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.05.00152

Düz vantuz (oval)

SGO 30x10 NBR-55 N022



Art.-Nr.: 10.01.05.00152



Teknik veriler

Attribute	Value
Vantuz malzemesi	Nitril kauçuk NBR
Malzeme sertliği [Shore A]	55.0 Shore A
Emme kuvveti (-600mbar)	12.20 N
Ağırlık	2.8 g
Boyutlar (LxW)	30 x 10
Ürün ailesi	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00152



Veri aksesuarları sipariş edin 10.01.05.00152

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N022 G1/8-AG DN350
Vantuz bağlantı nipel	SA-NIP N022 G1/8-IG DN350



WWW.SCHMALZ.COM/10.01.05.00152