


Düz vantuz (oval)

SGO 7x3.5 HT1-60 N003


Art.-Nr.: 10.01.05.00427



SGO 7x3.5 HT1-60 N003

Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Boyutlar (LxW)	7 x 3,5
Malzeme özelliği	iz bırakmayan



Tasarım verileri SGO 7x3.5 HT1-60 N003

Tasarım verileri

Attribute	Value
Yükseklik H2	1.50 mm
Yükseklik H	6.00 mm
Kafa çapı Dk	6.0 mm
Nominal çap dn	1.50 mm
İç çap d	1.50 mm
Yay stroku Z	0.8 mm
Vantuz genişliği Bs	3.50 mm
Ls	7.00 mm
Lmaks.(S)	7.50 mm
Bmax(S)	4.50 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.05.00427

Düz vantuz (oval)

SGO 7x3.5 HT1-60 N003



Art.-Nr.: 10.01.05.00427



Teknik veriler

Attribute	Value
Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60.0 Shore A
Emme kuvveti (-600mbar)	1.00 N
Ağırlık	0.2 g
Boyutlar (LxW)	7 x 3,5
Ürün ailesi	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00427



Veri aksesuarları sipariş edin 10.01.05.00427

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N003 M3-AG DN100
	10.01.01.00316



WWW.SCHMALZ.COM/10.01.05.00427