

Flat suction cup (oval)

SGO 15x5 HT1-60 N021


Art.-Nr.: 10.01.05.00429



SGO 15x5 HT1-60 N021

Technical data

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Dimension (LxW)	15 x 5
Material property	non-marking



Design data SGO 15x5 HT1-60 N021

Design data

Attribute	Value
Height H2	3.00 mm
Height H	12.00 mm
Head diameter Dk	8.5 mm
Nominal diameter dn	1.20 mm
Internal diameter d1	6.0 mm
Internal diameter d	4.50 mm
Spring stroke Z	0.7 mm
Height H3	5.50 mm
Suction cup width Bs	4.60 mm
Ls	14.60 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3



WWW.SCHMALZ.COM/10.01.05.00429

Art.-Nr.: 10.01.05.00429

**Technical data**

Attribute	Value
Suction cup material	High temperature material HT1
Material hardness [Shore A]	60.0 Shore A
Suction force (-600mbar)	3.10 N
Weight	0.4 g
Dimension (LxW)	15 x 5
Product family	SGO

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.05.00429

**Ordering Data Accessories 10.01.05.00429**

Typ		Item number
Suction cup connection nipple	SA-NIP N021 M5-AG DN200	10.01.05.00126
Suction cup connection nipple	SA-NIP N021 M5-IG DN200	10.01.05.00125

