

Düz vantuz (oval)

SGO 60x20 HT1-60 N023


Art.-Nr.: 10.01.05.00440



SGO 60x20 HT1-60 N023

Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Boyutlar (LxW)	60x20
Malzeme özelliği	iz bırakmayan



Tasarım verileri SGO 60x20 HT1-60 N023

Tasarım verileri

Yükseklik H2	8,00 mm
Yükseklik H	21,00 mm
Kafa çapı Dk	15,5 mm
Nominal çap dn	4,00 mm
İç çap d1	13,0 mm
İç çap d	11,50 mm
Yay stroku Z	2,5 mm
Yükseklik H3	10,00 mm
Vantuz genişliği Bs	19,00 mm
Ls	59,00 mm
Lmaks.(S)	61,00 mm
Bmax(S)	22,00 mm

Not: DIN ISO 3302-1 M3 uyarınca elastomer parçalar için kabul edilebilir boyut toleransları



WWW.SCHMALZ.COM/10.01.05.00440

Düz vantuz (oval)

SGO 60x20 HT1-60 N023



Art.-Nr.: 10.01.05.00440



Teknik veriler

Vantuz malzemesi	Yüksek sıcaklık malzemesi HT1
Malzeme sertliği [Shore A]	60,0 Shore A
Emme kuvveti (-600mbar)	50,10 N
Ağırlık	6,40 g
Ürün ailesi	SGO
Boyutlar (LxW)	60x20

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Sipariş Verisi Aksesuarlar 10.01.05.00440

Typ	Ürün numarası
Vantuz bağlantı nipel	SA-NIP N023 G1/4-AG DN350 10.01.05.00122
Vantuz bağlantı nipel	SA-NIP N023 G1/4-IG DN350 10.01.05.00121



WWW.SCHMALZ.COM/10.01.05.00440